

Modular components

Transparent cover for immediate diagnostics

Simple and easy programming / handling

Programming, Diagnosis and data-recording via Palm Top

5 tubes for high capacity

Anti-manipulation devices

Free programmable tube levels



## Model

**SC5€ DUAL**

### Technical data:

Protocol	MDB; EXE/ DEX / 24 Volt AC
Acceptance	5 ¢, 10 ¢, 20 ¢, 50 ¢, 1 €, 2 € 2 free vend,- 1 credit token
Temperature range	-15°C to + 60°C
Max. humidity	90 %
Power consumption	Stand by 2,6 VA, max. 7,7 VA
Voltage	Min. 20,4 Volt, max. 26,4 Volt
Change	4 different coins out of 5 tubes

### Capacities:

Tube A	50 ¢	23 to 61
Tube B	10 ¢	76
Tube C	20 ¢	70
Tube D	5 ¢	86
Tube E	5 ¢ or 10 ¢	86 or 76

### Dimensions and weights:

Height (mm)	380
Width (mm)	140
Depth (mm)	84
Weight	1800 gr

### Standard:

DIL-switchboard for fast configuration  
 Programming mode to reject false coins  
 Programming mode for 2 free vend and 1 credit token  
 Liquid rejection  
 Palm-interface (from version E)  
 DEX-interface with jack plug

### Options:

Conversion/ spacer kit 10 ¢ for tube E  
 Palmtop and accessories  
 Thermo-printer (DEX)



Vendo GmbH | Spangerstrasse 22 | D-40599 Düsseldorf  
 Fon: +49 (0)211-740 39-0 | Fax: +49 (0)211-748 85 41  
 Web: [www.vendo-europe.com](http://www.vendo-europe.com) | e-Mail: [infovdg@vendo-europe.com](mailto:infovdg@vendo-europe.com)